

item # model # project # sis # aia



HOLD HHT052E Warm holding cabinet

CONSTRUCTION FEATURES

- Tightness chamber with radiuses corners
- All-around rubber bumpers
- Total thermic insulation with rock or glass wood
- Long lasting front seal, made up of food-grade and high-heat resistant silicone
- Removable side racks to facilitate cleaning
- Static heating provided by low consumption wire heating element that coils up all the chamber
- Ergonomic and fully built-in door handle with magnetic closure
- Mounted on four 125 mm diameter castors, two of which with brake
- Ergonomic handle for pushing and guiding
- Easy access to facilitate maintenance and repair
- Opposite side opening

FUNCTIONAL FEATURES

- Electronic control of the temperature
- Operating temperature 30° ÷ 120°C
- Adjustable humidity vents on the door
- Chamber with safety thermostat
- Manual keyboard lock

STANDARD SUPPLY • Removable GN 2/1 and GN 1/1 tray racks

OPTIONS & ACCESSORIES

☐ Kit feet☐ Grids☐ Trays

MODULINESRL



TECHNICAL INSTALLATION DIAGRAM


Electricity supply cable inlet




Vent for excess humidity



Important - Drawing and dimensions refer to the standard version. They may change with the addition of accessories or options.





Overall dimensions
(W x D x H) - mm

Trays capacity - distance [mm]


Tray max. height GN 2/1 [mm]

Tray max. height GN 1/1 [mm]

Power supply

AC 220-240V 50/60Hz

740 x 840 x 735h	Total input [kW]	1,5 (230V)
5 x GN 2/1 - (75) 10 x GN 1/1 - (75)	Amps. [A]	6,6 (230V)
5 x 65 (h) 2 x 150 (h) 1 x 200 (h) + 2 x 65 (h)	Working temperature [°C]	30 ÷ 120
10 x 65 (h) 4 x 150 (h)	Product max capacity [Kg]	36
2 x 200 (h) + 4 x 65 (h)	Net weight [Kg]	51



- A Display
- B ON/OFF switch
- C Temperature decrease key
- D Temperature increase key
- E START/STOP key