



**HOLD**  
**HHT281E**  
 Warm holding cabinet

**CONSTRUCTION  
 FEATURES**

- Two separately controlled compartments
- All-around rubber bumpers
- Total thermic insulation with rock or glass wool
- Long lasting front seal, made up of food-grade and high-heat resistant silicone
- Removable side racks to facilitate cleaning
- Static heating provided by low consumption wire heating element that coils up all the chamber DELIWARM®
- Ergonomic and fully built-in door handles with magnetic closure
- Four swivel wheels of which 2 with brake
- Ergonomic handle for pushing and guiding
- Easy access to facilitate maintenance and repair

**FUNCTIONAL  
 FEATURES**

- Two separate electronic controls
- Operating temperature 30° ÷ 120°C
- Adjustable humidity vents on the doors
- Chamber with safety thermostat
- Manual keyboard lock

**STANDARD  
 SUPPLY**


- Removable GN 1/1 tray racks


**OPTIONS  
 & ACCESSORIES**

- Kit feet
- Grids
- Trays
- Opposite side opening
- UK plug




**TECHNICAL  
INSTALLATION  
DIAGRAM**

Electricity supply  
cable inlet 

Vent for excess  
humidity 

Important - Drawing and  
dimensions refer to the  
standard version.  
They may change with  
the addition of  
accessories  
or options.



**Overall dimensions**  
(W x D x H) - mm

555 x 730 x 1760 h

**Trays capacity -  
distance [mm]**

(8+8) x GN 1/1 - (75)

**Tray max. height  
[mm]**

8 x 65 (h) + 8 x 65 (h)  
3 x 150 (h) + 3 x 150 (h)  
2 x 200 (h) + 2 x 65 (h) and 2 x 200 (h) + 2 x 65 (h)

**Power supply**

AC 220-240V 50/60Hz

**Total input  
[kW]**

2 (230V)

**Amps.  
[A]**

8,7 (230V)

**Working  
temperature [°C]**

30 ÷ 120

**Product max  
capacity [Kg]**

58

**Net weight  
[Kg]**

88



- A Display
- B ON/OFF switch
- C Temperature decrease key
- D Temperature increase key
- E START/STOP key

MODULINESRL